

NTN

OPTIMAL SOLUTIONS

for your applications



NTN®

SNR®

Brands of
NTN Group

INNOVATION AT YOUR PRODUCTION'S SERVICE


Movement. It is constantly changing. It is analysed, brought under control, guided and mastered with the aim of deriving maximum benefit. It is more than merely a concept. It is the very essence of our commitment, namely designing and innovating to deliver the perfect solutions to the issues and constraints of today and tomorrow.

There are thousands of us around the world masterminding and developing solutions to raise the bar on your production performance. Our world-leading brands (**NTN**, **BCA**, **BOWER** and **SNR**) are marketed worldwide and deliver the best-fit solutions for working together and building a more environmentally-friendly society. Follow our lead and use interaction, anticipation and adaptation as the keys to guiding and shaping the future of the manufacturing, automotive and aviation markets.

5.05 BILLION €*
of turnover*

22,000*
employees

The local service of an international partner



117
Sales
representations

72
Production
sites

15
R&D
centres

* March 2025



For more information,
click here

High precision bearings

Japanese excellence made in Germany

- **Wide range of high precision bearings** (angular contact ball, cylindrical roller) and ball screw support bearings **for demanding applications**.
- **High-end packaging ready for digitalization (integrated QR code)** / Innovative design / Higher rotation speeds / Longer service life / Eco-friendly solutions.
- Reduced maintenance costs / Higher productivity and efficiency / Great flexibility thanks to **European production**.



For more information,
click here

Ball Bearings

The strengths of this range

- Over **10,000 references** (bore diameters from 1.5 to 1,320 mm).
- **Premium quality steel** for optimum service life.
- **A complete range of sealing solutions.**
- **High-tech products** (Topline, Megahom™...) to meet **the most specific requirements**.



For more information,
click here

Tapered roller bearings

The 2-in-1 offer (inch and metric)

- **Over 3,000 references in metric and inch** (bore up to 1,270 mm)
- 9 main dimensional series in metric dimensions with **standard angles**, plus 4 series with **increased angles**.
- Very wide range of inch dimensions: **over 200 series, and cones and cups can be managed as separate elements** in addition to the assembled bearing.
- **Through-hardened or case-hardened steel** (100% of the range in inch dimensions is case-hardened steel).



For more information,
click here

Mounted units

A full assortment of advantages

- **Over 40,000 standard units providing** a multitude of solutions.
- **Bearing units (12 to 140 mm):** various sealing options. Available with European and Asian designs.
- **Two-part plummer block housings** (20 to 500 mm shaft diameter): single or multiple bearings with grease or oil-lubrication. Also available as «ready for use» kit (spherical roller bearing + accessories inside).



For more information,
click here

Linear motion

The solution for all linear moving needs

- **Expansive range of linear motion** (linear guides, linear axes, ball screw and linear ball bushings in metric and inch dimensions) customized or standard for every industrial need.
- Unique technical features availables / Quick availability of customized solutions / **Wide range of tools (online configurator)**.

A wide range of solutions

to accompany customers throughout product life



SERVICES

A STRONG LINK WITH OUR CUSTOMERS

NTN Europe provides solutions to accompany customers throughout product life: training, elearning technical supports, bearing diagnosis, Bebox...

For more information,
click here

Partnership is a NTN core value.

Cylindrical roller bearings

The ULTAGE™ label for ultimate performances

- **2,000 references, with 1 row of rollers** (bore from 20 to 1,250 mm, with or without cage), **2 rows** (bore from 25 to 500 mm, with or without cage) and **4 rows** (bore from 100 to 1,030 mm).
- The core of the single-row range under the ULTAGE™ label, to offer the best performance: **increased service life (+20%)** thanks to **increased load capacities (+7%)** / Capacities among the highest on the market / **Speed increased by 20%**.



For more information,
click here

Spherical roller bearings

Reliability and robustness

- Over **2,000 references** (25 to 2000 mm inner diameter).
- **3 types of bearing: open, sealed or closed by defectors (KIZEI®)**, Low noise option, EF800 range for applications with high vibration levels.
- **Reliability and longer service life:** cost reduction.



For more information,
click here

Needle roller bearings

The reference range made in Japan

- **12 families and 8,000 items** (bore diameter from 5 to 400 mm) widest range of the market.
- **100% made in Japan** / Superior steel quality / Sturdy design: constant manufacturing quality.
- **Extended service life (up to x3)** / Absolute reliability / European logistics centre for short delivery times.



For more information,
click here

Lubrication

Fully suited solutions

- Greases and oils / Automatic single-point and multi-point lubrication systems / Advice and set-up services.
- **Dedicated lubrication systems and lubricants** for each application.
- **LUBSOLID, solid lubrication** for all products and markets. **SENTINEL™, a range dedicated to the food industry.**
- **Increased bearing service life, machine availability and productivity.**



For more information,
click here

Maintenance tools

Fitting and removing bearings

- **Complete range of tools** for cold and hot mounting, hydraulic mounting and dismounting, extractors, safety and measuring instruments.
- Products designed **to meet specific requirements**.
- **Lower operating costs:** a better equipment availability thanks to adapted and professional tools.



For more information,
click here

NTN

Make the world **NAMERAKA**

DOC_I_CORP_ARG2 GBb - Code SAP : 706881 - Document non contractuel - NTN Europe copyright international - 07/25-Photos : NTN Europe - Pedro Studio Photos

This document is the exclusive property of NTN Europe. Any total or partial reproduction hereof without the prior consent of NTN Europe is strictly prohibited. Legal action may be brought against anyone breaching the terms of this paragraph.
NTN Europe shall not be held liable for any errors or omissions that may have crept into this document despite the care taken in drafting it. Due to our policy of continuous research and development, we reserve the right to make changes without notice to all or part of the products and specifications mentioned in this document.
© NTN Europe, international copyright 2025.

NTN Europe - 1 rue des Usines - 74000 Annecy
RCS ANNECY B 325 821 072 - Code APE 2815Z - Code NACE 28.15
www.ntn-europe.com

NTN®

SNR®

BCA™
BEARINGS

BOWER®

Brands of
NTN Group