



Brand of NTN Group



# SNC BEARING KITS FOR CONVEYORS

QUARRIES, MINES & CEMENT PLANTS



CREATED TO INCREASE  
PRODUCTIVITY, PERFORMANCE  
AND RELIABILITY IN HARSH  
ENVIRONMENTS

OPT FOR THE  
ALL-IN-ONE



Benefits of kit

- Modular kit with all accessories (Cover and locating rings included)
- Simplified logistics with a single reference to manage
- Cheaper to buy in kit form than as individual



## SNC BEARING KITS + ULTAGE SEALED BEARING



Plummer block accessories  
**FREE**



### Low operating and maintenance costs

- Protection of the bearing against liquid/solid pollution
- Drastically reduced regreasing requirements (zero in some cases)

Designation	d	Plummer block
	Shaft [mm]	SNC
KITSNC10X22208KEEDS	35	SNC 508-607
KITSNC10X22209KEEDS	40	SNC 509
KITSNC10X22210KEEDS	45	SNC 510-608
KITSNC10X22211KEEDS	50	SNC 511-609
KITSNC10X22212KEEDS	55	SNC 512-610
KITSNC10X22213KEEDS	60	SNC 513-611
KITSNC10X22215KEEDS	65	SNC 515-612
KITSNC10X22216KEEDS	70	SNC 516-613
KITSNC10X22217KEEDS	75	SNC 517
KITSNC10X22218KEEDS	80	SNC 518-615

### Shaft diameters:

from 35 to 80 mm

### 20 KIT references available:

10 with standard CN clearance  
10 with standard C3 clearance

Upon request, other KIT configurations are possible

## SNC BEARING KITS + ULTAGE OPEN BEARING



Plummer block accessories  
**FREE**



### Make your life easier!

Complete basic offer

Optimised purchasing cost

Designation	d	Plummer block
	Shaft [mm]	SNC
KITSNC22208KDS/DB120HD	35	SNC 508-607
KITSNC22209KDS/DB120HD	40	SNC 509
KITSNC22210KDS/DB120HD	45	SNC 510-608
KITSNC22211KDS/DB120HD	50	SNC 511-609
KITSNC22212KDS/DB120HD	55	SNC 512-610
KITSNC22213KDS/DB120HD	60	SNC 513-611
KITSNC22215KDS/DB120HD	65	SNC 515-612
KITSNC22216KDS/DB120HD	70	SNC 516-613
KITSNC22217KDS/DB120HD	75	SNC 517
KITSNC22218KDS/DB120HD	80	SNC 518-615

### Shaft diameters:

from 35 to 80 mm

### 20 KIT references available:

10 with standard CN clearance  
10 with standard C3 clearance

Upon request, other KIT configurations are possible

This document is the exclusive property of NTN Europe. Any total or partial reproduction hereof without the prior consent of NTN Europe is strictly prohibited. Legal action may be brought against anyone breaching the terms of this paragraph. NTN Europe shall not be held liable for any errors or omissions that may have crept into this document despite the care taken in drafting it. Due to our policy of continuous research and development, we reserve the right to make changes without notice to all or part of the products and specifications mentioned in this document.  
© NTN Europe, international copyright 2024.

NTN Europe - 1 rue des Usines - 74000 Annecy  
RCS ANNECY B 325 821 072 - Code APE 2815Z - Code NACE 28.15  
[www.ntn-europe.com](http://www.ntn-europe.com)

**NTN** | **SNR** | Brands of NTN Group