Brand of **NTN Group**

# AGRIHUB

Your season with
complete peace of mind

AGRIHUB

**INSTALL IT, RUN IT, FORGET IT.**

# **Successful seasons**
# come from properly prepared soil

The choice of disc harrow hub can make all the difference.

Designed to offer you both efficiency and peace of mind, **AGRIHUB SNR l**ets you stay focused on what really matters to you: **he success of your crops.**

# SEALING

To withstand the numerous sources of pollution and prevent it penetrating inside, the **AGRIHUB SNR** is equipped with a complete sealing system consisting of:

**A high-performance sealing system**
designed and tested to our high standards



**8 sealing lips**
on the contaminated side



**INSTALL IT, RUN IT, FORGET IT.**

# HOUSING

The housing, which is directly exposed to the shocks and stresses of the ground, must provide mechanical strength and seals stability. It consists of:



## A forged steel housing

- selected for its resistant properties
- with a thick cross-section to protect the seal against impacts from stones

## Zinc coating

# Opting for peace of mind **is productivity-enhancing**

Choose NTN Europe's expertise in design and sealing for reliable equipment and remarkable productivity.



## Pollution is blocked from entering

Thanks to a sealed barrier consisting of 8 lips on the exposed side.

## Shock-resistant

Eviter les défaillances prématurées grâce à un moyeu épais et robuste.

## Ready to install and compatible

with a wide range of equipment.

# Available products

| References | Number of fixing holes | Diameter of the fixing holes | D | J | G | B1 | B2 | B | L1 | L2 | Disc diameter | Weight (kg) |
|---|---|---|---|---|---|---|---|---|---|---|---|---|
| **HUA151-4M12-S01** | 4 | M12x1.25 | 117 | 98 | M22x1.5 | 10 | 60 | 102 | 29 | 26 | < 700 | 2.00 |
| **HUA151-5M12-S01** | 5 | M12x1.25 | 117 | 98 | M22x1.5 | 10 | 60 | 102 | 29 | 26 | < 700 | 1.99 |
| **HUA151-6M12-S01** | 6 | M12x1.25 | 117 | 98 | M22x1.5 | 10 | 60 | 102 | 29 | 26 | < 700 | 1.98 |

▸ Contact us for any other requests.

# Equivalences

| Number of fixing holes | SNR hub | Equivalent hub |
|---|---|---|
| 4 | HUA151-4M12-S01 | SKF BAA-0004 (T100)<br>SKF BAA-0023 (T100)<br>SKF BAA-0044 (T200)<br>PEER AGHU2898X4E-DSCS (T50)<br>NSK AHU 28117A-01<br>FKL IL50-98/4T-M22 (or IL40)<br>INA F-673270.04.TILL<br>LFD AGRI.HUB 4<br>FLT PR040/4x98 |
| 5 | HUA151-5M12-S01 | SKF BAA-0012<br>SKF BAA-0047<br>PEER AGHU2898X5E-DSCS<br>NSK AHU 28117A-02<br>FKL IL50-98/5T-M22 (or IL40)<br>INA F-673270.05.TILL<br>PFI PHA0012 |
| 6 | HUA151-6M12-S01 | SKF BAA-0006<br>PEER AGHU2898X6E-DSCS<br>NSK AHU 28117A-03<br>FKL IL50-98/6T-M22 (or IL40)<br>INA F-673270.06.TILL |




DOC_I_AGRI_AGRI-HUB_FL2_140x148_GBb. - Document non contractuel - NTN Europe copyright international - 04/26 - Photos : NTNEurope - Pedro Studio Photos

This document is the exclusive property of NTN Europe. Any total or partial reproduction hereof without the prior consent of NTN Europe is strictly prohibited. Legal action may be brought against anyone breaching the terms of this paragraph.
NTN Europe shall not be held liable for any errors or omissions that may have crept into this document despite the care taken in drafting it. Due to our policy of continuous research and development, we reserve the right to make changes without notice to all or part of the products and specifications mentioned in this document.
© NTN Europe, international copyright 2026.

NTN Europe - 1 rue des Usines - 74000 Annecy
RCS ANNECY B 325 821 072 - Code APE 2815Z - Code NACE 28.15
**www.ntn-europe.com**

NTN | SNR | Brands of NTN Group